

64657 HLX

Low-voltage halogen lamps without reflector



Areas of application

- Lamps for special luminaires
- Medical fiber optics (HLX)

Product family benefits

- Compared to standard lamps up to 10 % higher luminous efficacy (HLX)
- Instant light (HLX)

Product family features

- Xenon instead of krypton as the filler gas (XENOPHOT HLX versions)
- Luminous flux up to 10 % higher with same power consumption (XENOPHOT HLX versions)
- HLX tungsten halogen low-voltage lamp with or without reflector
- Dimmable (HLX)





Product datasheet

Technical data

Product information

Electrical data

Nominal voltage	24.0 V
Nominal wattage	250.00 W

Photometrical data

Dimensions & weight

Diameter	13.5 mm
Length	55.0 mm
Light center length (LCL)	33.0 mm
Filament length	8.00 mm
Illuminated field	8.0*4.0 mm ²
Filament diameter	4.0 mm

Lifespan

Lifespan	300 h
----------	-------

Additional product data

Base (standard designation)	G6.35
Minimum diameter of lamp enclosure	14 mm

Capabilities

Dimmable	Yes
Burning position	s90

Certificates & standards

EEI – Energy Label	В
--------------------	---

Country specific categorizations


ANSI code	EVC
LIF	M/33
Order reference	64657 HLX

Product datasheet

Country specific information

Product code	METEL code	SEG number	STK number	UK Org
4050300012001	OSRH64657HLX	8327824	4736557	-
4050300012001	OSRH64657HLX	-	4736557	-

Product datasheet



Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300012001	64657 HLX	Folding carton box 1	25 mm x 23 mm x 70 mm	0.04 dm ³	5.34 g
4050300890821	64657 HLX	Shipping carton box 40	144 mm x 107 mm x 121 mm	1.86 dm ³	254.60 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.